



530 Series FETAL DOPPLER

Features

- Easy and convenient operation
- High-fidelity,crystal clear sound
- High sensitivity doppler probe
- Low ultrasound dosage
- Display with color LCD
- FHR with voice fundtion(option)
- Bluetooth APP(option)

Fetal Doppler

Technical Specification

Ultrasound frequency :2MHz/3MHz
Ultrasound intensity: < 10W/cm²
Power supply:
AA battery(for B ad G)
Rechargeable battery
AC 220/110V 50/60Hz(for D ad C)

FHR Measuring range:50~230bpm
FHR resolution:1bpm
FHR accuracy:±2bpm
Power consumption:<1W

530 Series



Function	530B	530D	530G	530C
Display	B/W	B/W	Color	Color
Backlight	Yes	Yes	Yes	Yes
Build-in speaker	Yes	Yes	Yes	Yes
Various work modes	No	No	Yes	Yes
Volume adjustment	Yes	Yes	Yes	Yes
Battery indicator	Yes	Yes	Yes	Yes
FHR display	Yes	Yes	Yes	Yes
FHR curve	No	No	Yes	Yes
Charge in device	No	Yes	No	Yes
Alkalinity battery	Yes	No	Yes	No
Rechargeable battery	No	Yes	No	Yes
Bluetooth	Option	Option	Option	Option
FHR voice function	Option	Option	Option	Option
Carry bag	Option	Option	Option	Option

All specifications are subject to change without notice.